

Recycling Material


TKS-34 

col : G·S·K/N·J·A/G




TKS-34MR  

col : S·K/N·A/G·WES




TKS-40 

col : S·K/N·J·A/G



TKS-340 


col : W·B·CR



W


TKS-35 

col : G·S·K/N·J·A/G




TKS-35MR  

col : S·K/N·A/G·WES




TKS-10 


col : W·B·CR




CR


TKS-36 

col : G·S·K/N·J·A/G




TKS-42 

col : S·K/N·J·A/G




NEW TKS-44 

col : G·QS·K/N·J·A/G




NEW TKS-440 

col : W·B




TKS-33 

col : G·S·K/N·J·A/G




NEW TKS-43 

col : QS·K/N·J·A/G




TKS-21 

col : S·K/N·J·A/G





HB-6000MR  

size : 8.5·10mm
col : S·A/G·K/N·WES





HB-6000 

size : 8.5·10mm
col : W·B·T00




TK-12 (ABS) (PA) 

ABS col : G · S · A/G · K/N-J
PA col : W · B




TK-11 (ABS) (PA) 

ABS col : G · S · A/G · K/N-J
PA col : W · B





TK-3 (ABS) (PA) 

ABS col : G · S · A/G · K/N-J
PA col : W · B · CR



BP-2 (ABS) 

col : G · S · A/G



HB-0020 (PA) 

size : 25 · 30 · 40 · 50 mm
col : W · B



25mm



30mm



40mm



50mm

SJR-0020 (ABS) 

size : 25 · 30 · 40 · 50 mm
col : G · S · A/G · A/S · K/N



G



S



A/G



A/S



K/N

*#K/N-Jについて: 耐腐食性を向上させるため#K/Nにジャブクリアー加工を施しております。